

**Garant****Left-hand thread blind hole machine tap, uncoated, Type: 9/16-24****Order data**

Order number	130041 9/16-24
GTIN	4062406046156
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread  $\varnothing$ : 14.288 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 11 mm

Shank square  $\square$ : 9 mm

Tapping hole  $\varnothing$ : 13.4 mm

**Technical description**

Thread $\varnothing$	14.288 mm
Tool material	HSS E
Shank square $\square$	9 mm
Overall length L	110 mm
Standard	DIN 376
Thread pitch	1.058 mm
Tapping hole $\varnothing$	13.4 mm

Threads per inch	24
Shank $\varnothing D_s$	11 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread depth	35.72 mm
Thread type	UNEF-LH
Thread size	9/16-24 UNEF LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap