

Garant**Blind hole machine tap, uncoated, Type: 1-10****Order data**

Order number	130040 1-10
GTIN	4062406044398
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread \varnothing : 25.4 mm

Overall length L: 160 mm

Shank \varnothing D_s: 20 mmShank square \square : 16 mmTapping hole \varnothing : 23 mm**Technical description**

Tapping hole \varnothing	23 mm
Overall length L	160 mm
Thread \varnothing	25.4 mm
Shank square \square	16 mm
Thread depth	63.5 mm
Number of cutting edges Z	4
Shank \varnothing D _s	20 mm

Threads per inch	10
Standard	DIN 376
Number of clamping slots	4
Thread pitch	2.54 mm
Tool material	HSS E
Thread type	UNS
Thread size	1-10 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap