

Garant
Blind hole machine tap, TiN, Type: 9/16-24

Order data

Order number	130045 9/16-24
GTIN	4062406048396
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNEF
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 24
 Thread \varnothing : 14.288 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 11 mm
 Shank square \square : 9 mm
 Tapping hole \varnothing : 13.4 mm

Technical description

Number of cutting edges Z	3
Thread pitch	1.058 mm
Tapping hole \varnothing	13.4 mm
Shank square \square	9 mm
Thread \varnothing	14.288 mm
Overall length L	110 mm
Tool material	HSS E

Threads per inch	24
Shank $\varnothing D_s$	11 mm
Standard	DIN 376
Number of clamping slots	3
Thread depth	35.72 mm
Thread type	UNEF
Thread size	9/16-24 UNEF
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap