

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 1.1/16-12****Order data**

Order number	130046 1.1/16-12
GTIN	4062406051167
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread  $\varnothing$ : 26.99 mm

Overall length L: 160 mm

Shank  $\varnothing$  D<sub>s</sub>: 20 mm

Shank square  $\square$ : 16 mm

Tapping hole  $\varnothing$ : 25 mm

**Technical description**

Thread depth	67.5 mm
Tapping hole $\varnothing$	25 mm
Threads per inch	12
Number of cutting edges Z	4
Overall length L	160 mm
Thread $\varnothing$	26.99 mm
Shank $\varnothing$ D <sub>s</sub>	20 mm

Shank square <input type="checkbox"/>	16 mm
Standard	DIN 376
Tool material	HSS E
Thread pitch	2.117 mm
Number of clamping slots	4
Thread type	UN-LH
Thread size	1.1/16-12 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap