

**Garant**
**Left-hand thread through hole machine tap, TiN, Type: 7/16-24**

**Order data**

Order number	130036 7/16-24
GTIN	4062406041526
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread  $\varnothing$ : 11.11 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 9 mm

Shank square  $\square$ : 7 mm

Tapping hole  $\varnothing$ : 10.1 mm

**Technical description**

Shank $\varnothing$ D <sub>s</sub>	9 mm
Number of clamping slots	3
Thread pitch	1.058 mm
Threads per inch	24
Thread $\varnothing$	11.11 mm
Tapping hole $\varnothing$	10.1 mm
Thread depth	33.33 mm

Number of cutting edges Z	3
Standard	DIN 376
Tool material	HSS E
Overall length L	110 mm
Shank square □	7 mm
Thread type	UNS-LH
Thread size	7/16-24 UNS LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap