

Garant**Left-hand thread blind hole machine tap, TiN, Type: 1.1/16-16****Order data**

Order number	130046 1.1/16-16
GTIN	4062406051150
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread Ø: 26.99 mm

Overall length L: 160 mm

Shank Ø D_s: 20 mm

Shank square □: 16 mm

Tapping hole Ø: 25.5 mm

Technical description

Shank square □	16 mm
Number of cutting edges Z	4
Tool material	HSS E
Number of clamping slots	4
Standard	DIN 376
Thread depth	67.5 mm
Thread Ø	26.99 mm

Tapping hole Ø	25.5 mm
Shank Ø D _s	20 mm
Overall length L	160 mm
Threads per inch	16
Thread pitch	1.588 mm
Thread type	UN-LH
Thread size	1.1/16-16 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap