

Garant
Blind hole machine tap, TiN, Type: 7/16-27

Order data

Order number	130045 7/16-27
GTIN	4062406048235
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 27
 Thread \varnothing : 11.112 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 9 mm
 Shank square \square : 7 mm
 Tapping hole \varnothing : 10.2 mm

Technical description

Shank \varnothing D _s	9 mm
Thread \varnothing	11.112 mm
Thread pitch	0.94 mm
Threads per inch	27
Shank square \square	7 mm
Number of clamping slots	3
Thread depth	27.78 mm

Number of cutting edges Z	3
Tool material	HSS E
Overall length L	110 mm
Standard	DIN 376
Tapping hole Ø	10.2 mm
Thread type	UNS
Thread size	7/16-27 UNS
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap