

Garant
Blind hole machine tap, uncoated, Type: 1.9/16-18

Order data

Order number	130040 1.9/16-18
GTIN	4062406044961
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread \varnothing : 39.688 mm

Overall length L: 200 mm

Shank \varnothing D_s: 32 mm

Shank square \square : 24 mm

Tapping hole \varnothing : 38.55 mm

Technical description

Number of cutting edges Z	4
Thread \varnothing	39.688 mm
Thread pitch	1.411 mm
Threads per inch	18
Overall length L	200 mm
Thread depth	99.22 mm
Shank square \square	24 mm

Shank $\varnothing D_s$	32 mm
Tool material	HSS E
Number of clamping slots	4
Tapping hole \varnothing	38.55 mm
Standard	DIN 376
Thread type	UNEF
Thread size	1.9/16-18 UNEF
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap