

Garant
Left-hand thread through hole machine tap, TiN, Type: 7/16-28

Order data

Order number	130036 7/16-28
GTIN	4062406041502
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNEF-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 28
 Thread \varnothing : 11.11 mm
 Overall length L: 110 mm
 Shank $\varnothing D_s$: 9 mm
 Shank square \square : 7 mm
 Tapping hole \varnothing : 10.35 mm

Technical description

Thread pitch	0.907 mm
Number of cutting edges Z	3
Number of clamping slots	3
Shank square \square	7 mm
Standard	DIN 376
Thread depth	33.33 mm
Shank $\varnothing D_s$	9 mm

Tool material	HSS E
Threads per inch	28
Overall length L	110 mm
Thread Ø	11.11 mm
Tapping hole Ø	10.35 mm
Thread type	UNEF-LH
Thread size	7/16-28 UNEF LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap