

**Garant****Blind hole machine tap, uncoated, Type: 1.1/2-10****Order data**

Order number	130040 1.1/2-10
GTIN	4062406044923
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D<sub>s</sub>: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 35.7 mm

**Technical description**

Standard	DIN 376
Number of clamping slots	4
Thread Ø	38.1 mm
Number of cutting edges Z	4
Overall length L	200 mm
Tool material	HSS E
Thread pitch	2.54 mm

Tapping hole Ø	35.7 mm
Shank square □	24 mm
Threads per inch	10
Shank Ø D <sub>s</sub>	32 mm
Thread depth	95.25 mm
Thread type	UNS
Thread size	1.1/2-10 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap