

Garant**Left-hand thread blind hole machine tap, TiN, Type: 1.1/4-24****Order data**

Order number	130046 1.1/4-24
GTIN	4062406051310
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread \varnothing : 31.75 mm

Overall length L: 180 mm

Shank \varnothing D_s: 25 mmShank square \square : 20 mmTapping hole \varnothing : 30.75 mm**Technical description**

Number of cutting edges Z	4
Shank \varnothing D _s	25 mm
Number of clamping slots	4
Threads per inch	24
Tapping hole \varnothing	30.75 mm
Tool material	HSS E
Overall length L	180 mm

Thread Ø	31.75 mm
Standard	DIN 376
Thread pitch	1.058 mm
Shank square □	20 mm
Thread depth	79.38 mm
Thread type	UNS-LH
Thread size	1.1/4-24 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap