

Garant**Left-hand thread through hole machine tap, TiN, Type: 1.5/8-12****Order data**

Order number	130036 1.5/8-12
GTIN	4062406042813
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread \varnothing : 41.275 mm

Overall length L: 200 mm

Shank \varnothing D_s: 32 mmShank square \square : 24 mmTapping hole \varnothing : 39.3 mm**Technical description**

Standard	DIN 376
Thread \varnothing	41.275 mm
Overall length L	200 mm
Number of clamping slots	4
Thread depth	82.55 mm
Number of cutting edges Z	4
Thread pitch	2.117 mm
Tool material	HSS E

Shank square □	24 mm
Shank Ø D _s	32 mm
Tapping hole Ø	39.3 mm
Threads per inch	12
Thread type	UN-LH
Thread size	1.5/8-12 UN LH
Coating	TiN
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap