

Garant
Left-hand thread blind hole machine tap, TiN, Type: 1.1/2-16

Order data

Order number	130046 1.1/2-16
GTIN	4062406051617
Item class	10N

Description
Note:

Delivery time: 49 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 16
 Thread \varnothing : 38.1 mm
 Overall length L: 200 mm
 Shank \varnothing D_s: 32 mm
 Shank square \square : 24 mm
 Tapping hole \varnothing : 36.6 mm

Technical description

Number of clamping slots	4
Thread depth	95.25 mm
Standard	DIN 376
Threads per inch	16
Thread pitch	1.588 mm
Tapping hole \varnothing	36.6 mm
Tool material	HSS E

Thread Ø	38.1 mm
Shank square □	24 mm
Overall length L	200 mm
Number of cutting edges Z	4
Shank Ø D _s	32 mm
Thread type	UN-LH
Thread size	1.1/2-16 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap