

**Garant**
**Blind hole machine tap, uncoated, Type: 15/16-12**

**Order data**

Order number	130040 15/16-12
GTIN	4062406044312
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread Ø: 23.812 mm

Overall length L: 160 mm

Shank Ø D<sub>s</sub>: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 21.8 mm

**Technical description**

Shank Ø D <sub>s</sub>	18 mm
Shank square □	14.5 mm
Number of cutting edges Z	4
Overall length L	160 mm
Threads per inch	12
Thread depth	59.53 mm
Tool material	HSS E

Standard	DIN 376
Number of clamping slots	4
Tapping hole Ø	21.8 mm
Thread Ø	23.812 mm
Thread pitch	2.117 mm
Thread type	UN
Thread size	15/16-12 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap