

Garant
Left-hand thread blind hole machine tap, TiN, Type: 1.1/2-18

Order data

| | |
|--------------|-----------------|
| Order number | 130046 1.1/2-18 |
| GTIN | 4062406051600 |
| Item class | 10N |

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread Ø: 38.1 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 36.9 mm

Technical description

| | |
|---------------------------|----------|
| Threads per inch | 18 |
| Number of clamping slots | 4 |
| Standard | DIN 376 |
| Number of cutting edges Z | 4 |
| Thread Ø | 38.1 mm |
| Thread depth | 95.25 mm |
| Overall length L | 200 mm |

| | |
|----------------------------------|--|
| Tapping hole Ø | 36.9 mm |
| Thread pitch | 1.411 mm |
| Tool material | HSS E |
| Shank square □ | 24 mm |
| Shank Ø D _s | 32 mm |
| Thread type | UNEF-LH |
| Thread size | 1.1/2-18 UNEF LH |
| Coating | TiN |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2×D for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |