

Garant**Left-hand thread blind hole machine tap, TiN, Type: 1.5/8-14****Order data**

Order number	130046 1.5/8-14
GTIN	4062406051761
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread \varnothing : 41.275 mm

Overall length L: 200 mm

Shank \varnothing D_s: 32 mmShank square \square : 24 mmTapping hole \varnothing : 39.5 mm**Technical description**

Thread pitch	1.814 mm
Tool material	HSS E
Threads per inch	14
Tapping hole \varnothing	39.5 mm
Number of cutting edges Z	4
Thread depth	103.19 mm
Overall length L	200 mm

Shank $\varnothing D_s$	32 mm
Number of clamping slots	4
Standard	DIN 376
Shank square \square	24 mm
Thread \varnothing	41.275 mm
Thread type	UNS-LH
Thread size	1.5/8-14 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap