

**Garant**
**Blind hole machine tap, uncoated, Type: 15/16-16**

**Order data**

Order number	130040 15/16-16
GTIN	4062406044305
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread Ø: 23.812 mm

Overall length L: 160 mm

Shank Ø D<sub>s</sub>: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 22.3 mm

**Technical description**

Thread depth	59.53 mm
Shank square □	14.5 mm
Shank Ø D <sub>s</sub>	18 mm
Overall length L	160 mm
Tool material	HSS E
Number of cutting edges Z	4
Threads per inch	16

Standard	DIN 376
Thread Ø	23.812 mm
Tapping hole Ø	22.3 mm
Thread pitch	1.588 mm
Number of clamping slots	4
Thread type	UN
Thread size	15/16-16 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap