

**Garant**
**Left-hand thread blind hole machine tap, TiN, Type: 3/4-12**

**Order data**

Order number	130046 3/4-12
GTIN	4062406050870
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days  
 Minimum order quantity: 2 pcs.  
 Special / custom-made product - return not possible  
 Thread type: UN-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 12  
 Thread  $\varnothing$ : 19.05 mm  
 Overall length L: 125 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 14 mm  
 Shank square  $\square$ : 11 mm  
 Tapping hole  $\varnothing$ : 17 mm

**Technical description**

Thread pitch	2.117 mm
Tool material	HSS E
Shank square $\square$	11 mm
Overall length L	125 mm
Number of clamping slots	4
Tapping hole $\varnothing$	17 mm
Standard	DIN 376

Shank $\varnothing D_s$	14 mm
Number of cutting edges Z	4
Threads per inch	12
Thread depth	47.63 mm
Thread $\varnothing$	19.05 mm
Thread type	UN-LH
Thread size	3/4-12 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap