

Garant
Blind hole machine tap, uncoated, Type: 1.5/8-24

Order data

Order number	130040 1.5/8-24
GTIN	4062406045005
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread \varnothing : 41.275 mm

Overall length L: 200 mm

Shank \varnothing D_s: 32 mm

Shank square \square : 24 mm

Tapping hole \varnothing : 40.35 mm

Technical description

Tool material	HSS E
Overall length L	200 mm
Shank \varnothing D _s	32 mm
Number of cutting edges Z	4
Number of clamping slots	4
Standard	DIN 376
Tapping hole \varnothing	40.35 mm

Shank square □	24 mm
Thread Ø	41.275 mm
Thread pitch	1.058 mm
Thread depth	103.19 mm
Threads per inch	24
Thread type	UNS
Thread size	1.5/8-24 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap