

Garant**Left-hand thread through hole machine tap, TiN, Type: 11/16-12****Order data**

Order number	130036 11/16-12
GTIN	4062406041847
Item class	10N

Description**Note:**

Delivery time: 49 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UN-LH
Tool material: HSS E
Standard: DIN 376
Threads per inch: 12
Thread \varnothing : 17.462 mm
Overall length L: 125 mm
Shank \varnothing D_s: 14 mm
Shank square \square : 11 mm
Tapping hole \varnothing : 15.5 mm

Technical description

Thread pitch	2.117 mm
Standard	DIN 376
Threads per inch	12
Thread depth	34.92 mm
Shank square \square	11 mm
Thread \varnothing	17.462 mm
Tapping hole \varnothing	15.5 mm

Shank $\varnothing D_s$	14 mm
Overall length L	125 mm
Number of cutting edges Z	3
Number of clamping slots	3
Tool material	HSS E
Thread type	UN-LH
Thread size	11/16-12 UN LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap