

**Garant**
**Left-hand thread blind hole machine tap, TiN, Type: 1.5/16-12**

**Order data**

Order number	130046 1.5/16-12
GTIN	4062406051433
Item class	10N

**Description**
**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread  $\varnothing$ : 33.338 mm

Overall length L: 200 mm

Shank  $\varnothing$  D<sub>s</sub>: 28 mm

Shank square  $\square$ : 22 mm

Tapping hole  $\varnothing$ : 31.3 mm

**Technical description**

Thread depth	83.3 mm
Thread $\varnothing$	33.338 mm
Threads per inch	12
Shank square $\square$	22 mm
Number of clamping slots	4
Shank $\varnothing$ D <sub>s</sub>	28 mm
Number of cutting edges Z	4

Overall length L	200 mm
Standard	DIN 376
Tool material	HSS E
Tapping hole Ø	31.3 mm
Thread pitch	2.117 mm
Thread type	UN-LH
Thread size	1.5/16-12 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap