

Garant**Left-hand thread through hole machine tap, TiN, Type: 7/8-16****Order data**

Order number	130036 7/8-16
GTIN	4062406042004
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread \varnothing : 22.23 mm

Overall length L: 140 mm

Shank \varnothing D_s: 18 mmShank square \square : 14.5 mmTapping hole \varnothing : 20.7 mm**Technical description**

Tapping hole \varnothing	20.7 mm
Threads per inch	16
Overall length L	140 mm
Tool material	HSS E
Shank \varnothing D _s	18 mm
Thread pitch	1.588 mm
Standard	DIN 376

Thread depth	66.69 mm
Shank square □	14.5 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread Ø	22.23 mm
Thread type	UN-LH
Thread size	7/8-16 UN LH
Coating	TiN
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap