

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 11/16-20****Order data**

Order number	130046 11/16-20
GTIN	4062406050788
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days  
Minimum order quantity: 2 pcs.  
Special / custom-made product - return not possible  
Thread type: UN-LH  
Tool material: HSS E  
Standard: DIN 376  
Threads per inch: 20  
Thread Ø: 17.462 mm  
Overall length L: 125 mm  
Shank Ø D<sub>s</sub>: 14 mm  
Shank square □: 11 mm  
Tapping hole Ø: 16.25 mm

**Technical description**

Thread pitch	1.27 mm
Standard	DIN 376
Thread Ø	17.462 mm
Number of clamping slots	4
Thread depth	43.7 mm
Shank square □	11 mm
Tool material	HSS E

Shank $\varnothing D_s$	14 mm
Tapping hole $\varnothing$	16.25 mm
Number of cutting edges Z	4
Overall length L	125 mm
Threads per inch	20
Thread type	UN-LH
Thread size	11/16-20 UN LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap