

Garant**Left-hand thread blind hole machine tap, TiN, Type: 3/4-16****Order data**

Order number	130046 3/4-16
GTIN	4062406050856
Item class	10N

Description**Note:**

Delivery time: 49 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 17.5 mm

Technical description

Number of clamping slots	4
Tapping hole Ø	17.5 mm
Tool material	HSS E
Thread Ø	19.05 mm
Threads per inch	16
Overall length L	125 mm
Shank Ø D _s	14 mm

Thread pitch	1.588 mm
Standard	DIN 376
Shank square □	11 mm
Number of cutting edges Z	4
Thread depth	47.63 mm
Thread type	UNF-LH
Thread size	3/4-16 UNF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap