

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 3/8-32****Order data**

Order number	130046 3/8-32
GTIN	4062406050399
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 32

Thread  $\varnothing$ : 9.525 mm

Overall length L: 100 mm

Shank  $\varnothing$  D<sub>s</sub>: 10 mmShank square  $\square$ : 8 mmTapping hole  $\varnothing$ : 8.85 mm**Technical description**

Standard	DIN 371
Number of clamping slots	3
Tapping hole $\varnothing$	8.85 mm
Thread depth	23.83 mm
Tool material	HSS E
Shank square $\square$	8 mm
Thread $\varnothing$	9.525 mm

Threads per inch	32
Shank $\varnothing D_s$	10 mm
Number of cutting edges Z	3
Thread pitch	0.794 mm
Overall length L	100 mm
Thread type	UNEF-LH
Thread size	3/8-32 UNEF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap