

Garant**Blind hole machine tap, uncoated, Type: 2-10****Order data**

Order number	130040 2-10
GTIN	4062406045418
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread Ø: 50.8 mm

Overall length L: 250 mm

Shank Ø D_s: 40 mm

Shank square □: 32 mm

Tapping hole Ø: 48.4 mm

Technical description

Thread depth	127 mm
Thread pitch	2.54 mm
Thread Ø	50.8 mm
Shank Ø D _s	40 mm
Threads per inch	10
Overall length L	250 mm
Tool material	HSS E

Tapping hole Ø	48.4 mm
Standard	DIN 376
Shank square □	32 mm
Number of cutting edges Z	4
Number of clamping slots	4
Thread type	UNS
Thread size	2-10 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap