

Garant
Blind hole machine tap, uncoated, Type: 5/8-24

Order data

Order number	130040 5/8-24
GTIN	4062406043988
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNEF
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 24
 Thread \varnothing : 15.875 mm
 Overall length L: 110 mm
 Shank \varnothing D_s: 12 mm
 Shank square \square : 9 mm
 Tapping hole \varnothing : 15 mm

Technical description

Thread depth	39.7 mm
Thread \varnothing	15.875 mm
Standard	DIN 376
Threads per inch	24
Shank square \square	9 mm
Thread pitch	1.058 mm
Tool material	HSS E

Shank $\varnothing D_s$	12 mm
Tapping hole \varnothing	15 mm
Number of cutting edges Z	3
Number of clamping slots	3
Overall length L	110 mm
Thread type	UNEF
Thread size	5/8-24 UNEF
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap