

Garant
Left-hand thread blind hole machine tap, TiN, Type: 2-14

Order data

Order number	130046 2-14
GTIN	4062406052119
Item class	10N

Description
Note:

Delivery time: 49 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread Ø: 50.8 mm

Overall length L: 250 mm

Shank Ø D_s: 40 mm

Shank square □: 32 mm

Tapping hole Ø: 49.25 mm

Technical description

Tapping hole Ø	49.25 mm
Number of cutting edges Z	4
Thread depth	127 mm
Shank square □	32 mm
Standard	DIN 376
Tool material	HSS E
Overall length L	250 mm

Shank $\varnothing D_s$	40 mm
Threads per inch	14
Thread \varnothing	50.8 mm
Thread pitch	1.814 mm
Number of clamping slots	4
Thread type	UNS-LH
Thread size	2-14 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap