

Garant**Blind hole machine tap, uncoated, Type: 11/16-24****Order data**

Order number	130040 11/16-24
GTIN	4062406044053
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNEF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 24

Thread \varnothing : 17.462 mm

Overall length L: 125 mm

Shank \varnothing D_s: 14 mmShank square \square : 11 mmTapping hole \varnothing : 16.6 mm**Technical description**

Thread depth	43.7 mm
Tapping hole \varnothing	16.6 mm
Standard	DIN 376
Number of cutting edges Z	4
Thread pitch	1.058 mm
Overall length L	125 mm
Number of clamping slots	4

Shank $\varnothing D_s$	14 mm
Shank square \square	11 mm
Thread \varnothing	17.462 mm
Tool material	HSS E
Threads per inch	24
Thread type	UNEF
Thread size	11/16-24 UNEF
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap