

Garant
Blind hole machine tap, uncoated, Type: 7/8-12

Order data

Order number	130040 7/8-12
GTIN	4062406044268
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 12
 Thread \varnothing : 22.225 mm
 Overall length L: 140 mm
 Shank \varnothing D_s: 18 mm
 Shank square \square : 14.5 mm
 Tapping hole \varnothing : 20.2 mm

Technical description

Tool material	HSS E
Number of clamping slots	4
Number of cutting edges Z	4
Thread depth	55.56 mm
Overall length L	140 mm
Thread \varnothing	22.225 mm
Thread pitch	2.117 mm

Shank $\varnothing D_s$	18 mm
Threads per inch	12
Shank square \square	14.5 mm
Tapping hole \varnothing	20.2 mm
Standard	DIN 376
Thread type	UN
Thread size	7/8-12 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap