

**Garant****Left-hand thread blind hole machine tap, TiN, Type: 1/4-28****Order data**

Order number	130046 1/4-28
GTIN	4062406050252
Item class	10N

**Description****Note:**

Delivery time: 49 calendar days

Minimum order quantity: 3 pcs.

Special / custom-made product - return not possible

Thread type: UNF-LH

Tool material: HSS E

Standard: DIN 371

Threads per inch: 28

Thread  $\varnothing$ : 6.35 mm

Overall length L: 80 mm

Shank  $\varnothing$  D<sub>s</sub>: 7 mmShank square  $\square$ : 5.5 mmTapping hole  $\varnothing$ : 5.5 mm**Technical description**

Standard	DIN 371
Number of cutting edges Z	3
Overall length L	80 mm
Shank square $\square$	5.5 mm
Tool material	HSS E
Thread $\varnothing$	6.35 mm
Tapping hole $\varnothing$	5.5 mm

Number of clamping slots	3
Threads per inch	28
Shank $\varnothing D_s$	7 mm
Thread depth	15.9 mm
Thread pitch	0.907 mm
Thread type	UNF-LH
Thread size	1/4-28 UNF LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap