

Garant**Blind hole machine tap, uncoated, Type: 7/16-14****Order data**

Order number	130040 7/16-14
GTIN	4062406043803
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNC

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread \varnothing : 11.112 mm

Overall length L: 110 mm

Shank \varnothing D_s: 9 mm

Shank square \square : 7 mm

Tapping hole \varnothing : 9.3 mm

Technical description

Number of cutting edges Z	3
Thread \varnothing	11.112 mm
Shank square \square	7 mm
Threads per inch	14
Thread pitch	1.814 mm
Number of clamping slots	3
Standard	DIN 376

Thread depth	27.78 mm
Shank $\varnothing D_s$	9 mm
Overall length L	110 mm
Tapping hole \varnothing	9.3 mm
Tool material	HSS E
Thread type	UNC
Thread size	7/16-14 UNC
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap