

**Garant**
**Blind hole machine tap, uncoated, Type: 3/4-16**

**Order data**

Order number	130040 3/4-16
GTIN	4062406044138
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNF

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D<sub>s</sub>: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 17.5 mm

**Technical description**

Tapping hole Ø	17.5 mm
Standard	DIN 376
Number of clamping slots	4
Thread depth	47.63 mm
Tool material	HSS E
Overall length L	125 mm
Threads per inch	16

Number of cutting edges Z	4
Thread Ø	19.05 mm
Shank square □	11 mm
Thread pitch	1.588 mm
Shank Ø D <sub>s</sub>	14 mm
Thread type	UNF
Thread size	3/4-16 UNF
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap