

Garant**Blind hole machine tap, uncoated, Type: 7/16-16****Order data**

Order number	130040 7/16-16
GTIN	4062406043797
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS E

Standard: DIN 376

Threads per inch: 16

Thread \varnothing : 11.112 mm

Overall length L: 110 mm

Shank \varnothing D_s: 9 mmShank square \square : 7 mmTapping hole \varnothing : 9.576 mm**Technical description**

Standard	DIN 376
Thread depth	27.78 mm
Tapping hole \varnothing	9.576 mm
Number of clamping slots	3
Tool material	HSS E
Overall length L	110 mm
Shank square \square	7 mm

Thread pitch	1.588 mm
Number of cutting edges Z	3
Threads per inch	16
Thread Ø	11.112 mm
Shank Ø D _s	9 mm
Thread type	UN
Thread size	7/16-16 UN
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap