

Garant
Blind hole machine tap, uncoated, Type: NO.10-56

Order data

Order number	130040 NO.10-56
GTIN	4062406043346
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 3 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 371
 Threads per inch: 56
 Thread \varnothing : 4.826 mm
 Overall length L: 70 mm
 Shank \varnothing D_s: 6 mm
 Shank square □: 4.9 mm
 Tapping hole \varnothing : 4.39 mm

Technical description

Overall length L	70 mm
Number of clamping slots	3
Tapping hole \varnothing	4.39 mm
Standard	DIN 371
Number of cutting edges Z	3
Shank \varnothing D _s	6 mm
Thread pitch	0.454 mm

Thread depth	12.1 mm
Tool material	HSS E
Thread Ø	4.826 mm
Threads per inch	56
Shank square □	4.9 mm
Thread type	UNS
Thread size	10-56 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap