

**Garant****Blind hole machine tap, uncoated, Type: 5/8-11****Order data**

Order number	130040 5/8-11
GTIN	4062406044046
Item class	10N

**Description****Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UNC

Tool material: HSS E

Standard: DIN 376

Threads per inch: 11

Thread  $\varnothing$ : 15.875 mm

Overall length L: 110 mm

Shank  $\varnothing$  D<sub>s</sub>: 12 mmShank square  $\square$ : 9 mmTapping hole  $\varnothing$ : 13.53 mm**Technical description**

Overall length L	110 mm
Shank $\varnothing$ D <sub>s</sub>	12 mm
Tool material	HSS E
Number of clamping slots	3
Number of cutting edges Z	3
Standard	DIN 376
Thread pitch	2.309 mm

Shank square □	9 mm
Thread Ø	15.875 mm
Tapping hole Ø	13.53 mm
Thread depth	39.7 mm
Threads per inch	11
Thread type	UNC
Thread size	5/8-11 UNC
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap