

Garant
Blind hole machine tap, uncoated, Type: 3/4-24

Order data

Order number	130040 3/4-24
GTIN	4062406044107
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNS
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 24
 Thread \varnothing : 19.05 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square \square : 11 mm
 Tapping hole \varnothing : 18.1 mm

Technical description

Thread \varnothing	19.05 mm
Number of clamping slots	4
Threads per inch	24
Thread pitch	1.058 mm
Shank square \square	11 mm
Thread depth	47.63 mm
Overall length L	125 mm

Standard	DIN 376
Tool material	HSS E
Tapping hole Ø	18.1 mm
Number of cutting edges Z	4
Shank Ø D _s	14 mm
Thread type	UNS
Thread size	3/4-24 UNS
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap