

Garant**Blind hole machine tap, uncoated, Type: 7/16-28****Order data**

Order number	130040 7/16-28
GTIN	4062406043742
Item class	10N

Description**Note:**

Delivery time: 35 calendar days
Minimum order quantity: 2 pcs.
Special / custom-made product - return not possible
Thread type: UNEF
Tool material: HSS E
Standard: DIN 376
Threads per inch: 28
Thread \varnothing : 11.112 mm
Overall length L: 110 mm
Shank $\varnothing D_s$: 9 mm
Shank square \square : 7 mm
Tapping hole \varnothing : 10.35 mm

Technical description

Thread \varnothing	11.112 mm
Threads per inch	28
Number of cutting edges Z	3
Tool material	HSS E
Thread depth	27.78 mm
Thread pitch	0.907 mm
Shank $\varnothing D_s$	9 mm

Standard	DIN 376
Tapping hole \varnothing	10.35 mm
Shank square \square	7 mm
Number of clamping slots	3
Overall length L	110 mm
Thread type	UNEF
Thread size	7/16-28 UNEF
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap