

**Garant**
**Left-hand thread blind hole machine tap, uncoated, Type: 1.5/16-20**

**Order data**

Order number	130041 1.5/16-20
GTIN	4062406046927
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread  $\varnothing$ : 33.338 mm

Overall length L: 200 mm

Shank  $\varnothing D_s$ : 28 mm

Shank square  $\square$ : 22 mm

Tapping hole  $\varnothing$ : 32.15 mm

**Technical description**

Number of cutting edges Z	4
Thread $\varnothing$	33.338 mm
Standard	DIN 376
Threads per inch	20
Shank $\varnothing D_s$	28 mm
Overall length L	200 mm
Number of clamping slots	4

Thread depth	83.3 mm
Thread pitch	1.27 mm
Tapping hole Ø	32.15 mm
Shank square □	22 mm
Tool material	HSS E
Thread type	UN-LH
Thread size	1.5/16-20 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap