

Garant**Left-hand thread blind hole machine tap, TiN, Type: NO.10-56****Order data**

Order number	130046 NO.10-56
GTIN	4062406050061
Item class	10N

Description**Note:**

Delivery time: 49 calendar days
Minimum order quantity: 3 pcs.
Special / custom-made product - return not possible
Thread type: UNS-LH
Tool material: HSS E
Standard: DIN 371
Threads per inch: 56
Thread \varnothing : 4.826 mm
Overall length L: 70 mm
Shank \varnothing D_s: 6 mm
Shank square □: 4.9 mm
Tapping hole \varnothing : 4.39 mm

Technical description

Thread \varnothing	4.826 mm
Thread pitch	0.454 mm
Number of clamping slots	3
Tapping hole \varnothing	4.39 mm
Number of cutting edges Z	3
Thread depth	12.1 mm
Standard	DIN 371

Threads per inch	56
Overall length L	70 mm
Shank $\varnothing D_s$	6 mm
Shank square \square	4.9 mm
Tool material	HSS E
Thread type	UNS-LH
Thread size	10-56 UNS LH
Coating	TiN
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap