

Garant
Machine tap for through holes and blind holes, uncoated, Type: 2.3/8-20

Order data

Order number	130050 2.3/8-20
GTIN	4062406052300
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN

Tool material: HSS

Threads per inch: 20

Thread \varnothing : 60.325 mm

Overall length L: 160 mm

Shank $\varnothing D_s$: 50 mm

Shank square \square : 39 mm

Tapping hole \varnothing : 59.12 mm

Technical description

Thread \varnothing	60.325 mm
Overall length L	160 mm
Threads per inch	20
Thread depth	90.49 mm
Thread pitch	1.27 mm
Shank $\varnothing D_s$	50 mm
Shank square \square	39 mm
Number of cutting edges Z	6

Tool material	HSS
Tapping hole Ø	59.12 mm
Number of clamping slots	6
Thread type	UN
Thread size	2.3/8-20 UN
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap