

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 1-10****Order data**

| | |
|--------------|---------------|
| Order number | 130041 1-10 |
| GTIN | 4062406046637 |
| Item class | 10N |

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNS-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 10

Thread \varnothing : 25.4 mm

Overall length L: 160 mm

Shank \varnothing D_s: 20 mmShank square \square : 16 mmTapping hole \varnothing : 23 mm**Technical description**

| | |
|----------------------------|---------|
| Shank square \square | 16 mm |
| Thread pitch | 2.54 mm |
| Number of clamping slots | 4 |
| Tapping hole \varnothing | 23 mm |
| Thread \varnothing | 25.4 mm |
| Threads per inch | 10 |
| Thread depth | 63.5 mm |

| | |
|----------------------------------|--|
| Overall length L | 160 mm |
| Shank $\varnothing D_s$ | 20 mm |
| Number of cutting edges Z | 4 |
| Standard | DIN 376 |
| Tool material | HSS E |
| Thread type | UNS-LH |
| Thread size | 1-10 UNS LH |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2xD for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |