

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 1.1/16-12****Order data**

Order number	130041 1.1/16-12
GTIN	4062406046682
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 12

Thread \varnothing : 26.99 mm

Overall length L: 160 mm

Shank \varnothing D_s: 20 mm

Shank square \square : 16 mm

Tapping hole \varnothing : 25 mm

Technical description

Tool material	HSS E
Thread \varnothing	26.99 mm
Tapping hole \varnothing	25 mm
Standard	DIN 376
Thread pitch	2.117 mm
Number of clamping slots	4
Thread depth	67.5 mm

Threads per inch	12
Overall length L	160 mm
Shank square □	16 mm
Shank Ø D _s	20 mm
Number of cutting edges Z	4
Thread type	UN-LH
Thread size	1.1/16-12 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap