

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 1.1/16-20

Order data

Order number	130041 1.1/16-20
GTIN	4062406046651
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 20
 Thread \varnothing : 26.99 mm
 Overall length L: 160 mm
 Shank \varnothing D_s: 20 mm
 Shank square \square : 16 mm
 Tapping hole \varnothing : 25.8 mm

Technical description

Number of clamping slots	4
Thread \varnothing	26.99 mm
Thread pitch	1.27 mm
Overall length L	160 mm
Shank \varnothing D _s	20 mm
Shank square \square	16 mm
Number of cutting edges Z	4

Tapping hole Ø	25.8 mm
Standard	DIN 376
Threads per inch	20
Tool material	HSS E
Thread depth	67.5 mm
Thread type	UN-LH
Thread size	1.1/16-20 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap