

**Garant**
**Left-hand thread blind hole machine tap, uncoated, Type: 15/16-20**

**Order data**

Order number	130041 15/16-20
GTIN	4062406046538
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread  $\varnothing$ : 23.812 mm

Overall length L: 160 mm

Shank  $\varnothing$  D<sub>s</sub>: 18 mm

Shank square  $\square$ : 14.5 mm

Tapping hole  $\varnothing$ : 22.7 mm

**Technical description**

Shank $\varnothing$ D <sub>s</sub>	18 mm
Shank square $\square$	14.5 mm
Number of clamping slots	4
Tapping hole $\varnothing$	22.7 mm
Thread pitch	1.27 mm
Threads per inch	20
Thread $\varnothing$	23.812 mm

Number of cutting edges Z	4
Tool material	HSS E
Overall length L	160 mm
Thread depth	59.53 mm
Standard	DIN 376
Thread type	UNEF-LH
Thread size	15/16-20 UNEF LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap