

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 1.5/8-18****Order data**

Order number	130041 1.5/8-18
GTIN	4062406047269
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: UNEF-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 18

Thread Ø: 41.275 mm

Overall length L: 200 mm

Shank Ø D_s: 32 mm

Shank square □: 24 mm

Tapping hole Ø: 40.1 mm

Technical description

Overall length L	200 mm
Number of cutting edges Z	4
Thread pitch	1.411 mm
Threads per inch	18
Tool material	HSS E
Thread depth	103.19 mm
Number of clamping slots	4

Shank $\varnothing D_s$	32 mm
Shank square \square	24 mm
Thread \varnothing	41.275 mm
Standard	DIN 376
Tapping hole \varnothing	40.1 mm
Thread type	UNEF-LH
Thread size	1.5/8-18 UNEF LH
Coating	uncoated
Flank angle	60°
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap