

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 3/4-16

Order data

| | |
|--------------|---------------|
| Order number | 130041 3/4-16 |
| GTIN | 4062406046378 |
| Item class | 10N |

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 2 pcs.
 Special / custom-made product - return not possible
 Thread type: UNF-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 16
 Thread \varnothing : 19.05 mm
 Overall length L: 125 mm
 Shank \varnothing D_s: 14 mm
 Shank square \square : 11 mm
 Tapping hole \varnothing : 17.5 mm

Technical description

| | |
|------------------------------------|---------|
| Tapping hole \varnothing | 17.5 mm |
| Tool material | HSS E |
| Number of cutting edges Z | 4 |
| Shank square \square | 11 mm |
| Number of clamping slots | 4 |
| Overall length L | 125 mm |
| Shank \varnothing D _s | 14 mm |

| | |
|----------------------------------|--|
| Thread Ø | 19.05 mm |
| Threads per inch | 16 |
| Thread depth | 47.63 mm |
| Standard | DIN 376 |
| Thread pitch | 1.588 mm |
| Thread type | UNF-LH |
| Thread size | 3/4-16 UNF LH |
| Coating | uncoated |
| Flank angle | 60 ° |
| Thread standard | ASME B1.1 |
| Tolerance class | 1B |
| Tolerance class | 2B +0.20 |
| Tolerance class | 2B +0.10 |
| Tolerance class | 3B |
| Tolerance class | 2B |
| Tolerance class | 2B +0.05 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 2×D for blind holes |
| Cutting direction | left-hand |
| Type of threading tool | Machine tap for conventional machining |
| Colour ring | without |
| Type of product | Tap |