

Garant
Left-hand thread blind hole machine tap, uncoated, Type: 1.9/16-8

Order data

Order number	130041 1.9/16-8
GTIN	4062406047238
Item class	10N

Description
Note:

Delivery time: 35 calendar days
 Minimum order quantity: 1 pc.
 Special / custom-made product - return not possible
 Thread type: UN-LH
 Tool material: HSS E
 Standard: DIN 376
 Threads per inch: 8
 Thread \varnothing : 39.688 mm
 Overall length L: 200 mm
 Shank \varnothing D_s: 32 mm
 Shank square \square : 24 mm
 Tapping hole \varnothing : 36.7 mm

Technical description

Thread depth	99.22 mm
Number of clamping slots	4
Thread pitch	3.175 mm
Number of cutting edges Z	4
Overall length L	200 mm
Threads per inch	8
Shank square \square	24 mm

Shank $\varnothing D_s$	32 mm
Thread \varnothing	39.688 mm
Tapping hole \varnothing	36.7 mm
Standard	DIN 376
Tool material	HSS E
Thread type	UN-LH
Thread size	1.9/16-8 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap