

Garant**Left-hand thread blind hole machine tap, uncoated, Type: 11/16-20****Order data**

Order number	130041 11/16-20
GTIN	4062406046309
Item class	10N

Description**Note:**

Delivery time: 35 calendar days

Minimum order quantity: 2 pcs.

Special / custom-made product - return not possible

Thread type: UN-LH

Tool material: HSS E

Standard: DIN 376

Threads per inch: 20

Thread Ø: 17.462 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 16.25 mm

Technical description

Overall length L	125 mm
Shank Ø D _s	14 mm
Tool material	HSS E
Thread depth	43.7 mm
Number of cutting edges Z	4
Tapping hole Ø	16.25 mm
Shank square □	11 mm

Thread pitch	1.27 mm
Standard	DIN 376
Threads per inch	20
Number of clamping slots	4
Thread Ø	17.462 mm
Thread type	UN-LH
Thread size	11/16-20 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap