

**Garant**
**Left-hand thread blind hole machine tap, uncoated, Type: 1.5/8-20**

**Order data**

Order number	130041 1.5/8-20
GTIN	4062406047252
Item class	10N

**Description**
**Note:**

Delivery time: 35 calendar days  
 Minimum order quantity: 1 pc.  
 Special / custom-made product - return not possible  
 Thread type: UN-LH  
 Tool material: HSS E  
 Standard: DIN 376  
 Threads per inch: 20  
 Thread  $\varnothing$ : 41.275 mm  
 Overall length L: 200 mm  
 Shank  $\varnothing$  D<sub>s</sub>: 32 mm  
 Shank square  $\square$ : 24 mm  
 Tapping hole  $\varnothing$ : 40.08 mm

**Technical description**

Number of clamping slots	4
Number of cutting edges Z	4
Tool material	HSS E
Thread $\varnothing$	41.275 mm
Thread depth	103.19 mm
Shank square $\square$	24 mm
Overall length L	200 mm

Threads per inch	20
Standard	DIN 376
Shank $\varnothing D_s$	32 mm
Thread pitch	1.27 mm
Tapping hole $\varnothing$	40.08 mm
Thread type	UN-LH
Thread size	1.5/8-20 UN LH
Coating	uncoated
Flank angle	60 °
Thread standard	ASME B1.1
Tolerance class	1B
Tolerance class	2B +0.20
Tolerance class	2B +0.10
Tolerance class	3B
Tolerance class	2B
Tolerance class	2B +0.05
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap